



## Short range distance sensors (displacement) OD Precision, RS-422

OD5-30T05



**Model Name** > **OD5-30T05**  
**Part No.** > **6035977**




#### At a glance

- Many measurement ranges from 24 mm ... 26 mm up to 300 mm ... 700 mm
- CMOS receiving element for measurement independent of surface
- High measuring accuracy and frequency
- Glass thickness measurement with just one sensor head
- Different light spot sizes
- Integrated calculations for up to three sensors
- Stand alone use via RS-422

#### Your benefits

- Non-contact measurement improves quality inspection during production
- Surface-independent measurement algorithms ensure minimum machine downtime, regardless of surface gloss or color
- Reduced processing times as a result of the high measuring frequency of up to 10 kHz
- Simple, cost-effective solution for challenging measuring tasks due to a variety of sensor models
- Optional stand-alone operation via RS-422 means the OD Precision offers maximum performance at lower investment costs
- High visibility LC display enables simple, cost-effective setup
- Many interfaces for simple integration into an existing production environment



#### Features

System part: Sensor head

#### Performance

|                                   |                                                              |
|-----------------------------------|--------------------------------------------------------------|
| Measuring range:                  | 25 mm ... 35 mm, 6 % ... 90 % remission; at default settings |
| Resolution:                       | 0.2 $\mu\text{m}$ <sup>1)</sup>                              |
| Repeatability:                    | 0.6 $\mu\text{m}$ <sup>2)</sup>                              |
| Linearity:                        | $\pm 8 \mu\text{m}$ <sup>3)</sup>                            |
| Response time <sup>4), 5)</sup> : | 0.1 ms                                                       |
| Measuring frequency:              | 10 kHz <sup>6)</sup>                                         |
| Light source:                     | Laser, red                                                   |
| Laser protection class:           | 2 (EN 60825-1) <sup>7)</sup>                                 |
| Typ. light spot size (distance):  | 30 $\mu\text{m}$ x 100 $\mu\text{m}$ (30 mm)                 |

|                      |                                                                                                                                                                                                                     |
|----------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Additional function: | Anti interference mode, Automatic sensitivity adjustment, Selectable measuring frequency (automatic/0.1 ms ... 3.2 ms), Glass thickness measurement, Manual sensitivity adjustment, Averaging settings 1 ... 4,096x |
| Output rate:         | 0.1 ms                                                                                                                                                                                                              |
| Note:                | OD Precision sensor head can be used with AOD5-P/N1 or stand-alone via RS-422                                                                                                                                       |

1) 3) Measurement on 90 % remission (ceramic, white), for OD5-25x measurement on mirror; averaging set to: 4096 2) Measurement on 90 % remission (ceramic, white), for OD5-25x measurement on mirror; averaging set to: 4096; constant ambient conditions 4) Time needed for automatic sensitivity adjustment is calculated as: sampling period x 20. At default setting 100  $\mu$ s (10kHz) this is  $\leq$  2ms. 5) 6) Default setting for OD5-350x100 and OD5-500x200 = 0.8 ms, 1.25 kHz likewise, all other types = 0.1 ms/10 kHz 7) Wavelength 655 nm, max. output 1 mW

## Interfaces

|                  |               |
|------------------|---------------|
| Data interface:  | RS-422        |
| Laser off input: | 1 x laser-off |

## Mechanics/electronics


|                          |                                                    |
|--------------------------|----------------------------------------------------|
| Connection type:         | 0.5 m cable with connector 1)                      |
| Supply voltage $V_s$ 2): | DC 12 V ... 24 V                                   |
| Warm-up time:            | $\leq$ 5 min                                       |
| Indication:              | LEDs, 4" color-display on optional controller unit |
| Weight:                  | 250 g 3)                                           |
| Housing material:        | Aluminum housing with glass lens                   |

1) Extensible by cable to max. 50 m 2) DC 12 V (-5 %) ... DC 24 V (+10 %) 3) Inclusive 0.5 m cable


## Ambient data

|                                     |                                                                 |
|-------------------------------------|-----------------------------------------------------------------|
| Enclosure rating:                   | IP 67                                                           |
| Protection class:                   | III                                                             |
| Ambient temperature:                | Operation: -10 ... 50 °C, Storage: -20 ... 60 °C                |
| Temperature drift:                  | $\pm$ 0.01 % FS/K (FS = Full Scale = Measuring range of sensor) |
| Typ. ambient light safety:          | Artificial light: $\leq$ 3,000 lx<br>Sunlight: $\leq$ 10,000 lx |
| Vibration resistance:               | 10 Hz ... 55 Hz (amplitude 1.5 mm, x-, y-, z-axis 2 hours each) |
| Shock resistance:                   | 50 G (x-, y-, z-axis 3 times each)                              |
| Relative humidity (not condensing): | 35 % ... 85 %                                                   |

Dimensional drawing




Adjustment possible




Connection type



Connection diagram




Light spot size



All dimensions in mm (inch)

Linearity



**Australia**

Phone +61 3 9457 0600  
1800 334 802 – tollfree  
E-Mail sales@sick.com.au

**Belgium/Luxembourg**

Phone +32 (0)2 466 55 66  
E-Mail info@sick.be

**Brasil**

Phone +55 11 3215-4900  
E-Mail sac@sick.com.br

**Canada**

Phone +1 905 771 14 44  
E-Mail information@sick.com

**Ceská Republika**

Phone +420 2 57 91 18 50  
E-Mail sick@sick.cz

**China**

Phone +86 4000 121 000  
E-Mail info.china@sick.net.cn  
Phone +852-2153 6300  
E-Mail ghk@sick.com.hk

**Danmark**

Phone +45 45 82 64 00  
E-Mail sick@sick.dk

**Deutschland**

Phone +49 211 5301-301  
E-Mail kundenservice@sick.de

**España**

Phone +34 93 480 31 00  
E-Mail info@sick.es

**France**

Phone +33 1 64 62 35 00  
E-Mail info@sick.fr

**Great Britain**

Phone +44 (0)1727 831121  
E-Mail info@sick.co.uk

**India**

Phone +91-22-4033 8333  
E-Mail info@sick-india.com

**Israel**

Phone +972-4-6801000  
E-Mail info@sick-sensors.com

**Italia**

Phone +39 02 27 43 41  
E-Mail info@sick.it

**Japan**

Phone +81 (0)3 3358 1341  
E-Mail support@sick.jp

**Magyarország**

Phone +36 1 371 2680  
E-Mail office@sick.hu

**Nederlands**

Phone +31 (0)30 229 25 44  
E-Mail info@sick.nl

**Norge**

Phone +47 67 81 50 00  
E-Mail austefjord@sick.no

**Österreich**

Phone +43 (0)22 36 62 28 8-0  
E-Mail office@sick.at

**Polska**

Phone +48 22 837 40 50  
E-Mail info@sick.pl

**România**

Phone +40 356 171 120  
E-Mail office@sick.ro

**Russia**

Phone +7-495-775-05-30  
E-Mail info@sick.ru

**Schweiz**

Phone +41 41 619 29 39  
E-Mail contact@sick.ch

**Singapore**

Phone +65 6744 3732  
E-Mail admin@sicksgp.com.sg

**Slovenija**

Phone +386 (0)1-47 69 990  
E-Mail office@sick.si

**South Africa**

Phone +27 11 472 3733  
E-Mail info@sickautomation.co.za

**South Korea**

Phone +82 2 786 6321/4  
E-Mail info@sickkorea.net

**Suomi**

Phone +358-9-25 15 800  
E-Mail sick@sick.fi

**Sverige**

Phone +46 10 110 10 00  
E-Mail info@sick.se

**Taiwan**

Phone +886-2-2375-6288  
E-Mail sales@sick.com.tw

**Türkiye**

Phone +90 (216) 528 50 00  
E-Mail info@sick.com.tr

**United Arab Emirates**

Phone +971 (0) 4 8865 878  
E-Mail info@sick.ae

**USA/México**

Phone +1(952) 941-6780  
1 800-325-7425 – tollfree  
E-Mail info@sickusa.com

More representatives and agencies  
at [www.sick.com](http://www.sick.com)