



## Smart light grids SAS

SAS4-S044P3PS2W00



**Model Name** > [SAS4-S044P3PS2W00](#)  
**Part No.** > [1211104](#)



#### At a glance

- Variable detection lengths from 120 mm up to 600 mm (in 160 mm increments)
- Set parameters via teach-in with no PC
- Simple teach-in setup
- Maximum range 4 m
- Response time 18 ms
- 25 mm resolution with 40 mm beam separation possible
- Highly immune to sunlight up to 150,000 lx
- Small blind zone < 11 mm

#### Your benefits

- Small, slim and sleek design enables easy integration into applications
- Capacitive teach-in button and LEDs make commissioning easier for complex solutions
- Slim and flat models offer flexible mounting options and optimize space while reducing damage
- Customized preset configurations or set parameters via one-touch teach-in with no PC
- Optical synchronization eliminates the need to lay cables, saving time
- Auto-teach and auto-muting enable Plug & Play. And, an alignment aid and “Click & Go” provide faster installation.



#### Features

|                                  |                       |
|----------------------------------|-----------------------|
| Technology:                      | Sender/receiver       |
| Task:                            | Switching light grid  |
| Minimum detectable object (MDO): | Parallel beam: ≥45 mm |
| Beam separation:                 | 40 mm                 |
| Optical light exit:              | Slim                  |

|                           |                                                  |
|---------------------------|--------------------------------------------------|
| Number of beams:          | 12                                               |
| Detection height:         | 440 mm                                           |
| Cross beam/parallel beam: | Parallel beam active                             |
| Output 1:                 | Output 1 active, if light beam interrupted       |
| Automatic teach:          | Automatic teach inactive                         |
| Alignment aid:            | Without alignment aid                            |
| Muting function:          | Muting function inactive                         |
| Configuration:            | Without teach button with configuration software |

## Performance

|                |                       |
|----------------|-----------------------|
| Maximum range: | 4 m <sup>1)</sup>     |
| Minimum range: | Parallel beam: ≥0 mm  |
| Response time: | Parallel beam: ≥19 ms |
| Working range: | 3 m                   |

<sup>1)</sup> No reserve for environmental issue and deterioration of the diode

## Interfaces

|                  |                                      |
|------------------|--------------------------------------|
| Output type:     | 1 x PNP                              |
| Inputs:          | Teach input                          |
| Connection type: | Short cable with connector M8, 4-pin |

## Mechanics/electronics

|                                   |                                                                                                       |
|-----------------------------------|-------------------------------------------------------------------------------------------------------|
| Wave length:                      | IR 950 nm                                                                                             |
| Supply voltage Vs:                | DC 24 V <sub>...</sub> , ± 20 %                                                                       |
| Power consumption sender:         | 112 mA <sup>1)</sup>                                                                                  |
| Power consumption receiver:       | 70 mA <sup>2)</sup>                                                                                   |
| Ripple:                           | < 5 Vpp                                                                                               |
| Output current I <sub>max</sub> : | 100 mA                                                                                                |
| Output load capacitive:           | 100 nF                                                                                                |
| Output load inductive:            | 1 H                                                                                                   |
| Initialization time:              | 1 s                                                                                                   |
| Dimensions (W x H x D):           | 25 mm x 512.4 mm x 8 mm                                                                               |
| Housing material:                 | PMMA                                                                                                  |
| Indication:                       | LED                                                                                                   |
| Synchronization:                  | Optical                                                                                               |
| Enclosure rating:                 | IP 65                                                                                                 |
| Circuit protection:               | Output Q short-circuit protected, Interference suppression, VS connections reverse-polarity protected |
| Weight:                           | 60 g                                                                                                  |
| Power consumption:                | 112 mA <sup>3)</sup>                                                                                  |
| Aluminum stabilizer:              | With stabilizer                                                                                       |
| Switching frequency:              | 500 kHz                                                                                               |

<sup>1) 2) 3)</sup> Without load

## Ambient data

|                       |                                                          |
|-----------------------|----------------------------------------------------------|
| Protection class:     | III                                                      |
| EMC:                  | EN 60947-5-2                                             |
| Ambient temperature:  | Operation: -25 ... 55 °C, Storage: -25 ... 70 °C         |
| Ambient light safety: | Direct: ≥100,000 lx, Indirect: ≥150,000 lx <sup>1)</sup> |
| Vibration resistance: | 5 g, 10 Hz ... 55 Hz (IEC 68-2-6)                        |


Shock load:

10 g/DIN EN 60068-2-29/16 ms

1) Sunlight


## Dimensional drawing

Slim, with stabilizer




- |1| Last beam
- |2| Beam separation RM
- |3| DH - Detection height (n x 40 mm) - RM
- |4| First beam
- |5| Connection
- |6| Same distance
- |7| n = beam
- |8| m = mounting hole


## Adjustments




## Anschlussart und -schema



### Sender



### Receiver



**Australia**

Phone +61 3 9457 0600  
1800 334 802 – tollfree  
E-Mail sales@sick.com.au

**Belgium/Luxembourg**

Phone +32 (0)2 466 55 66  
E-Mail info@sick.be

**Brasil**

Phone +55 11 3215-4900  
E-Mail sac@sick.com.br

**Canada**

Phone +1 905 771 14 44  
E-Mail information@sick.com

**Ceská Republika**

Phone +420 2 57 91 18 50  
E-Mail sick@sick.cz

**China**

Phone +86 4000 121 000  
E-Mail info.china@sick.net.cn  
Phone +852-2153 6300  
E-Mail ghk@sick.com.hk

**Danmark**

Phone +45 45 82 64 00  
E-Mail sick@sick.dk

**Deutschland**

Phone +49 211 5301-301  
E-Mail kundenservice@sick.de

**España**

Phone +34 93 480 31 00  
E-Mail info@sick.es

**France**

Phone +33 1 64 62 35 00  
E-Mail info@sick.fr

**Great Britain**

Phone +44 (0)1727 831121  
E-Mail info@sick.co.uk

**India**

Phone +91-22-4033 8333  
E-Mail info@sick-india.com

**Israel**

Phone +972-4-6801000  
E-Mail info@sick-sensors.com

**Italia**

Phone +39 02 27 43 41  
E-Mail info@sick.it

**Japan**

Phone +81 (0)3 3358 1341  
E-Mail support@sick.jp

**Magyarország**

Phone +36 1 371 2680  
E-Mail office@sick.hu

**Nederlands**

Phone +31 (0)30 229 25 44  
E-Mail info@sick.nl

**Norge**

Phone +47 67 81 50 00  
E-Mail austefjord@sick.no

**Österreich**

Phone +43 (0)22 36 62 28 8-0  
E-Mail office@sick.at

**Polska**

Phone +48 22 837 40 50  
E-Mail info@sick.pl

**România**

Phone +40 356 171 120  
E-Mail office@sick.ro

**Russia**

Phone +7-495-775-05-30  
E-Mail info@sick.ru

**Schweiz**

Phone +41 41 619 29 39  
E-Mail contact@sick.ch

**Singapore**

Phone +65 6744 3732  
E-Mail admin@sicksgp.com.sg

**Slovenija**

Phone +386 (0)1-47 69 990  
E-Mail office@sick.si

**South Africa**

Phone +27 11 472 3733  
E-Mail info@sickautomation.co.za

**South Korea**

Phone +82 2 786 6321/4  
E-Mail info@sickkorea.net

**Suomi**

Phone +358-9-25 15 800  
E-Mail sick@sick.fi

**Sverige**

Phone +46 10 110 10 00  
E-Mail info@sick.se

**Taiwan**

Phone +886-2-2375-6288  
E-Mail sales@sick.com.tw

**Türkiye**

Phone +90 (216) 528 50 00  
E-Mail info@sick.com.tr

**United Arab Emirates**

Phone +971 (0) 4 8865 878  
E-Mail info@sick.ae

**USA/México**

Phone +1(952) 941-6780  
1 800-325-7425 – tollfree  
E-Mail info@sickusa.com

More representatives and agencies  
at [www.sick.com](http://www.sick.com)